

Unit E, 3 Tudor Road, Altrincham Business Park, Cheshire, WA14 5RZ

Tel: 0161 975 9002 Email: sales@friedmans.co.uk Web: www.friedmans.co.uk

Technical Data Sheet

Article Meryl

Composition 91% POLYAMIDE 9% ELASTANE

 $\begin{array}{lll} \mbox{Weight m}^2 \ (+/- \, 5\%) & \mbox{200 g/m}^2 \\ \mbox{Weight linear m.} & \ (+/- \, 5\%) & \mbox{310 g/m lin.} \\ \mbox{Total width} \ (+/- \, 2\%) & \mbox{155 cm} \\ \end{array}$

Dimensional Stability – Washing 40° C width -5% MAX length -6% MAX BS EN ISO 6330 -@40°C - flat dry

Stretch to Dynamometer (+/- 10%)

NU Martindale - ISO 12945-2 7000 rotations

ZWICK – load 1.5 kg – strip test – size of the tested sample :

width **100**% length **75**%

(min 99% - max 121%) (min 68% - max 83%)

Modulus 40% width **110-205g** length **150-280g**

Resistance to pilling on fabric 4/5 on wool 2

Care labelling codes:





Pilling Resistant



Excellent UV Protection



Four Way Stretch



Breathable



Perfect Fit



Extra Comfort



Ultra Chlorine Resistant



Excellent Coverage





Resistance sun cream and oil Pilling Resistant

Notes:

Technical Specification details prior to a print or foil application.

Please note due to the numerous different Industries we supply, we cannot perform tests to everyone's requirement therefore we strongly recommend you carry out your own tests.

We recommend testing each dyebath before any treatment or application other than cutting and sewing. To improve our products, we reserve to modify these, as and when necessary.